


cps
432

Pack à porter.

The most innovative
secondary packaging
machinery.

Versatile. Fast. Eco-friendly.



Bags of diapers adult & baby
or femine care, pack of tissue roll
and other type of products.



cps
400
SERIES

cpscompany.it

Packaging material thickness:

| | |
|--------------------------|---|
| Polyethylene (PE): | from 35 to 90 My (microns) Density 0,87/0,93; Different film thickness TBD |
| Max. poly reel diameter: | Up to 450 mm |
| Max. poly reel width: | Up to 1850 mm |



Change-over time:

Max. 25 min. - based on staff training and performances.

Operating panel HMI

Boom mounted rotating "HMI" enabling machine control and management.
The system allows to:

- ✓ Monitor technical functions, check them and adjust them for optimum performance.
- ✓ Store format parameters in order to facilitate format changeovers.
- ✓ Detect the trouble shooting machine diagnostics.
- ✓ In English and Italian (on request in addition the customer's language)

Finished Bundle dimensions

| | |
|-------------------|---|
| Width | 180 mm - 350 mm (with ACTIVE PULL TECH 240 mm - 350mm) |
| Length | 180 mm - 600 mm or 1200* mm |
| Height | 100 mm - 250 mm (fold tissue) 65 mm - 250 mm (feminine care) |
| Overlapping | 50/60 mm |
| Pitch (length) | max 1400 mm |
| Handle (optional) | 50/60 mm |
| Max Reel (width) | 1850 mm |

Product handling:

Collating unit
(fold tissue - femine care)

Manual loading
(fold tissue - femine care)

Bundle Speed:


Up to 30 cycles/min

*Up to 16 cycles/min with a double stroke insertion sequence.

NB: : Production speed depends on the quality of the product coming from up-stream, on packaging material characteristics and final bundle dimensions required.



COST SAVING



VERSATILE




SUSTAINABLE



4.0 TECHNOLOGY

CPS 432 SUGGESTED FLOOR PLAN

Feminine care



Napkins and fold producty

